

CRISTALI, II/III & IV

ACIDS BY DBI

GLASS
DECORATIVE
TECHNIQUES
DBI

Soft and sensual, traditional acids add warmth to glass, providing sparkle for your exclusive projects. Three shades for a unique finish.

CRISTALI, **velvety soft.**
CRISTALI II/III, **sensuality of satin.**
CRISTALI IV, **exclusively diaphanous.**

Many personalized variations are possible for a contrasting, prestigious result, using these three treatments.

Description

CRISTALI, II/III and IV treatments change the aspect of glass giving it a translucent, smooth, silky appearance.

Use

Glass that is treated with CRISTALI, II/III and IV helps create personalized soft, private and elegant atmospheres for residential or professional areas.

Glass that is treated with CRISTALI, II/III and IV can be used in many ways:

- doors, windows, partitions;
- wall coverings;
- shower enclosures;
- furniture, worktops, table or desk tops, closet doors;
- stair steps, floor tiles.

Advantages

Personalization

CRISTALI, II/III and IV acid etchings can be entirely personalized. They provide many possibilities to harmonize with the area in which they are used:

- alternating transparent and translucent effects;


- use of different acid shades with or without clear etching;
- for making logos, patterns or designs of your choice;
- combined with other DBI surface treatments (such as LAKOPAK or LAKTRANS).

Beauty and light

Glass that is treated with CRISTALI, II/III and IV create refined beauty that ensures diffused light while preserving privacy of the area.

Easy maintenance

Glass that is treated with CRISTALI, II/III and IV are much easier to clean and maintain in comparison to other acid etchings.



Range

DBI'S CRISTALI, II/III and IV acid treatments are only made-to-measure.

DBI offers three uniform acid shades, from the whitest (CRISTALI) to the most translucent (CRISTALI IV). These shades can be combined on the same glass in order to create selected designs. The acid treatment can also be done on both sides of the glass.

It also exists in two granito shades of acid, CRISTALV (glossy) and CRISTALVI (mat).

Patterns and designs

A catalogue of patterns and designs is available, however customers may also ask for vectorization of their own illustrations.

Glass media

Personalized acid treatments can be applied to most glass media, shaped or not:

- clear glass;
- extra clear glass;
- tinted glass;
- printed glass (treatment on smooth side);
- coated glass;
- clear and colored mirror;
- laminated glass;
- tempered glass;
- dual windowpanes.

Dimensions and thicknesses

There are no limits on dimension and thickness for treatment except for those that are inherent to the glass media that is used.

Transformation

After CRISTALI, II/III and IV acid treatment, glass can be shaped, tempered, laminated, (satin side should not be in contact with PVB), curved. Assembled in dual windowpanes, it is preferable to place the treated side on side 4 (inside). It cannot be placed on the inner-space (sides 2 or 3) unless it is left untreated on the area that comes into contact with the double windowpanes' rubber seal.